


Fully variable and efficient valve train for reciprocating engines



Invention

The invention consists of an electrohydraulic actuation method for variable lift control and individual timing for gas exchange valves of reciprocating engines. Its main advantages are a low activation energy demand as well as an intelligent hydraulic system layout. This enables the control of the valve movements by simple hydraulic elements without the need for sophisticated feedback control action.



Background

Internal combustion engines profit from variable gas exchange valves in terms of efficiency, performance, optimized boosting concepts, lower exhaust emissions, enhanced cold start strategies, and compatibility with alternative fuels. The efficiency gain by unthrottled operation with full valve flexibility on a classical passenger car spark ignition passenger engine is in the order of 25% for relevant low load operating points, around 15% in relevant driving cycles, and still more than 5% in hybrid powertrains. Additionally, full valve flexibility gives the possibility to implement new combustion concepts such as (partially) premixed compression ignition.

Today's serial production, variable valve actuation (VVA) systems – still based on camshafts – only show limited variability in valve lift profiles despite of their complex mechanical setup. Known camless approaches, however, have not yet found the way into serial production mostly due to their high level of activation energy demand and/or complexity in design and control. The following feature profile shows the assessment of this invention versus known existing approaches:

Advantages

- Very low control effort: simple on/off switching of the solenoids (one per valve actuator) is needed, no requirement for ultra-fast solenoids.
- Optimum activation energy utilization and recuperation: energy demand is lower compared to camshaft operated valve trains.
- Load control from one to the next engine cycle.
- Soft landing.
- The desired valve lift can be either controlled by setting the actuation pressure level or by involving a direct lift limiting mechanism capable of handling high cylinder pressures as well as misfiring.
- State of the art valve springs guarantee for safe operation, even at electrical failures.
- Capable for use of alternative hydraulic fluids, e.g. water/glycol.
- The following Figure depicts the motion sequence:



Applications

This invention can be used on all kinds of internal combustion engines (spark ignition, compression ignition, alternative combustion concepts), as well as on other reciprocating compression or expansion machines with need for full variability in the gas exchange process.

Ownership

Empa, Swiss Federal Laboratories for Materials Testing and Research, Überlandstrasse 129, CH-8600 Dübendorf; Schneider Ingenieurbüro, Dufourstrasse 3, CH-3600 Thun; Patents pending

References

- Zsiga N., Omanovic A., Soltic P., Schneider W., FlexWork – Lastregelung bei einem Motor mit elektrohydraulischem, vollvariablen Ventiltrieb, 11. MTZ-Fachtagung «Ladungswechsel und Emissionierung», Stuttgart 2018
- Zsiga N., Omanovic A., Soltic P., Schneider W., Wirkungsgradvorteile beim Ottomotor unter Verwendung einer nockenwellenlosen, vollvariablen Ventilsteuerung gegenüber gedrosseltem Betrieb, 8. VDI-Fachtagung Ventiltrieb und Zylinderkopf, Würzburg 2019
- Zsiga N., Omanovic A., Soltic P., Schneider W., Funktionsweise und Potenziale eines neuartigen, elektrohydraulischen Ventiltriebs, MTZ Motortechnische Zeitschrift 09/2019

Keywords

Electro-hydraulic valve actuation, internal combustion engine, variable valve timing, variable valve actuation

Contact

Empa, Technology Transfer
Dr Andreas Kündig, andreas.kuendig@empa.ch
Phone +41 58 765 48 30, Fax +41 58 765 69 08

Technical Information

Dr Patrik Soltic
Laboratory for Automotive Powertrain Technologies
patrik.soltic@empa.ch
Phone +41 58 765 46 24, Fax +41 58 765 69 41



Empa

Materials Science and Technology

Empa

CH-8600 Dübendorf
Überlandstrasse 129

Telefon +41 58 765 11 11
Telefax +41 58 765 11 22

CH-9014 St. Gallen
Lerchenfeldstrasse 5

Telefon +41 58 765 74 74
Telefax +41 58 765 74 99

CH-3602 Thun
Feuerwerkerstrasse 39

Telefon +41 58 765 11 33
Telefax +41 58 765 69 90

www.empa.ch

Empa is an interdisciplinary research and service institution within the ETH Domain covering selected fields of materials science and technology development including important environmental issues. Empa's R&D activities focus on the requirements of industry and the needs of society, thus linking research to engineering, and science to industry and society. As a result, Empa is capable of providing its partners with customized services and solutions that not only enhance their innovative edge, but also help to improve the quality of life for the public at large. Safety, reliability and sustainability of materials and systems are cross-sectional topics and a hallmark of all Empa activities. As such, Empa plays a key role in Switzerland's research and innovation landscape.